

Garant GRIDLINE

Heavy-duty cabinet with Viewing window sliding door, Height: 1000mm**Order data**

Order number	942367 1000
GTIN	4062406072582
Item class	9GI

Description**Version:**

Equipped cabinet in 80x28G.

Reinforced side walls to take **reinforced storage shelves for 200 kg** at 25 mm intervals.

Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. Cabinets with reinforced cabinet base, without a levelling base.

Supplied with:

Cabinet with storage shelves.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves for GridLine heavy-duty cabinets see No. 942610.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Handle positioning	top
Depth in G	28
Usable height	845 mm
Weight	173 kg
Width in G	80

Depth	700 mm
Height	1000 mm
ComfortClose	no
Electronic locking system can be retrofitted	yes
Width	2000 mm
Shelf load capacity / maximum distributed shelf load (on metal)	200 kg
Number of shelves	4
Material thickness	1 mm
Cabinet housing internal load capacity	1600 kg
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Heavy-duty cabinet

Accessories

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 40G Drawer front height 200 mm	942583 200
Extended lighting set for GridLine cabinets with Sliding doors, width 80G for cabinet height 1000/1250 mm	940515 1000/1250
Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 40G Drawer front height 100 mm	942583 100
Lock plate for GridLine Type GP21	914227 GP21
Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 40G Drawer front height 150 mm	942583 150
	942583 125

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets
Width 40G Drawer front height 125 mm

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets
Width 40G Drawer front height 75 mm

942583 75

Heavy load shelf for cabinet / compartment width in G 40

942610 40

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets
Width 40G Drawer front height 300 mm

942583 300

Shelf clip set for GridLine cabinets
20 pieces Type F

940559 F