

Garant GRIDLINE

**Large-capacity / heavy-duty cabinet with Plain sheet metal swing door,
Height: 2000mm****Order data**

Order number	942721 2000
GTIN	4062406072650
Item class	9GI

Description**Version:**

Empty cabinet in 40×28G. Suitable drawers: 36×24G (please order these separately). Mountings for shelves at 25 mm intervals. Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves and accessories for GridLine large-capacity cabinets and heavy-duty cabinets see No. 942530 – 942610 and Group 95.

Use as a heavy-duty cabinet is only possible in conjunction with heavy load shelf No. 942610.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Width	1000 mm
Depth in G	28

ComfortClose	no
Usable height	1845 mm
Electronic locking system can be retrofitted	yes
Handle positioning	centre
Weight	119 kg
Width in G	40
Depth	700 mm
Height	2000 mm
Cabinet fronts	Plain sheet metal swing door
Type of cabinet	Base cabinet
Version	for individual configuration
Material thickness	0.9 mm
Cabinet housing internal load capacity	1600
Door opening angle	250 degrees
Height adjustment interval	25
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Large-capacity cabinet

Accessories

Drawers for swing-door large-capacity cabinets and heavy-duty cabinets Width 40G Drawer front height 75 mm	942573 75
Slide handle for GridLine Type GP11	914226 GP11
Inclined shelf foreForm for cabinet / compartment width in G 40	942550 40
Drawers for swing-door large-capacity cabinets and heavy-duty cabinets Width 40G Drawer front height 200 mm	942573 200
	942573 300

Drawers for swing-door large-capacity cabinets and heavy-duty cabinets
Width 40G Drawer front height 300 mm

Drawers for swing-door large-capacity cabinets and heavy-duty cabinets
Width 40G Drawer front height 150 mm

942573 150

Extended lighting set for GridLine cabinets with Swing doors, width 40G for cabinet height 2000 mm

940511 2000

Drawers for swing-door large-capacity cabinets and heavy-duty cabinets
Width 40G Drawer front height 100 mm

942573 100

Storage shelf with brackets 100 kg for cabinet / compartment width in G 40

942530 40

Drawers for swing-door large-capacity cabinets and heavy-duty cabinets
Width 40G Drawer front height 125 mm

942573 125

Basic lighting set for GridLine cabinets with swing doors for cabinet height 2000 mm

940501 2000