

Garant **GRIDLINE****Large-capacity / heavy-duty cabinet with Viewing window swing door,
Height: 2000mm****Order data**

Order number	942703 2000
GTIN	4062406072636
Item class	9GI

Description**Version:**

Empty cabinet in 30×28G. Suitable drawers: 26×24G (please order these separately). Mountings for shelves at 25 mm intervals. Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves and accessories for GridLine large-capacity cabinets and heavy-duty cabinets see No. 942530 – 942610 and Group 95.

Use as a heavy-duty cabinet is only possible in conjunction with heavy load shelf No. 942610.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Height	2000 mm
Width in G	30

Cabinet fronts	Viewing window swing door
Width	750 mm
Depth	700 mm
Depth in G	28
Electronic locking system can be retrofitted	yes
Type of cabinet	Base cabinet
Weight	107 kg
Usable height	1845 mm
Handle positioning	centre
ComfortClose	no
Version	for individual configuration
Material thickness	0.9 mm
Cabinet housing internal load capacity	1600
Door opening angle	250 degrees
Height adjustment interval	25
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Large-capacity cabinet

Accessories

Drawers for swing-door large-capacity cabinets and heavy-duty cabinets Width 30G Drawer front height 200 mm	942570 200
Basic lighting set for GridLine cabinets with swing doors for cabinet height 2000 mm	940501 2000
Drawers for swing-door large-capacity cabinets and heavy-duty cabinets Width 30G Drawer front height 125 mm	942570 125
Slide handle for GridLine Type GP11	914226 GP11
	942570 300

Drawers for swing-door large-capacity cabinets and heavy-duty cabinets
Width 30G Drawer front height 300 mm

Inclined shelf for cabinet / compartment width in G 30

942550 30

Storage shelf with brackets
100 kg for cabinet / compartment width in G 30

942530 30

Extended lighting set for GridLine cabinets with Swing doors, width 30G for cabinet height 2000 mm

940510 2000

Drawers for swing-door large-capacity cabinets and heavy-duty cabinets
Width 30G Drawer front height 75 mm

942570 75

Drawers for swing-door large-capacity cabinets and heavy-duty cabinets
Width 30G Drawer front height 150 mm

942570 150

Drawers for swing-door large-capacity cabinets and heavy-duty cabinets
Width 30G Drawer front height 100 mm

942570 100