

Garant GRIDLINE

**Large-capacity / heavy-duty cabinet with Plain sheet metal swing door,  
Height: 2000mm****Order data**

Order number	942701 2000
GTIN	4062406072612
Item class	9GI

**Description****Version:**

Empty cabinet in 30×28G. Suitable drawers: 26×24G (please order these separately). Mountings for shelves at 25 mm intervals. Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock.

**Colour:**

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

**Note:**

For storage shelves and accessories for GridLine large-capacity cabinets and heavy-duty cabinets see No. 942530 – 942610 and Group 95.

**Use as a heavy-duty cabinet is only possible in conjunction with heavy load shelf No. 942610.**

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

**Technical description**

Usable height	1845 mm
Width in G	30

Depth	700 mm
Width	750 mm
Weight	107 kg
Type of cabinet	Base cabinet
Height	2000 mm
ComfortClose	no
Handle positioning	centre
Cabinet fronts	Plain sheet metal swing door
Electronic locking system can be retrofitted	yes
Depth in G	28
Version	for individual configuration
Material thickness	0.9 mm
Cabinet housing internal load capacity	1600
Door opening angle	250 degrees
Height adjustment interval	25
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Large-capacity cabinet

## Accessories

Inclined shelf foreForm for cabinet / compartment width in G 30	942550 30
Drawers for swing-door large-capacity cabinets and heavy-duty cabinetsWidth 30G Drawer front height 100 mm	942570 100
Storage shelf with brackets100 kg for cabinet / compartment width in G 30	942530 30
Basic lighting set for GridLine cabinets withswing doors for cabinet height 2000 mm	940501 2000

Drawers for swing-door large-capacity cabinets and heavy-duty cabinetsWidth 30G Drawer front height 125 mm	942570 125
Drawers for swing-door large-capacity cabinets and heavy-duty cabinetsWidth 30G Drawer front height 200 mm	942570 200
Drawers for swing-door large-capacity cabinets and heavy-duty cabinetsWidth 30G Drawer front height 300 mm	942570 300
Drawers for swing-door large-capacity cabinets and heavy-duty cabinetsWidth 30G Drawer front height 150 mm	942570 150
Drawers for swing-door large-capacity cabinets and heavy-duty cabinetsWidth 30G Drawer front height 75 mm	942570 75
Extended lighting set for GridLine cabinets withSwing doors, width 30G for cabinet height 2000 mm	940510 2000
Slide handle for GridLine Type GP11	914226 GP11