

Garant GRIDLINE

**Large-capacity / heavy-duty cabinet with Plain sheet metal swing door,
Height: 1000mm****Order data**

Order number	942701 1000
GTIN	4062406072605
Item class	9GI

Description**Version:**

Empty cabinet in 30×28G. Suitable drawers: 26×24G (please order these separately). Mountings for shelves at 25 mm intervals. Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves and accessories for GridLine large-capacity cabinets and heavy-duty cabinets see No. 942530 – 942610 and Group 95.

Use as a heavy-duty cabinet is only possible in conjunction with heavy load shelf No. 942610.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Width	750 mm
Electronic locking system can be retrofitted	yes

Cabinet fronts	Plain sheet metal swing door
Depth	700 mm
Type of cabinet	Base cabinet
Width in G	30
ComfortClose	no
Weight	62 kg
Depth in G	28
Height	1000 mm
Usable height	845 mm
Handle positioning	top
Version	for individual configuration
Material thickness	0.9 mm
Cabinet housing internal load capacity	1600
Door opening angle	250 degrees
Height adjustment interval	25
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Large-capacity cabinet

Accessories

Slide handle for GridLine Type GP11	914226 GP11
Extended lighting set for GridLine cabinets with Swing doors, width 30G for cabinet height 1000/1250 mm	940510 1000/1250
Drawers for swing-door large-capacity cabinets and heavy-duty cabinets Width 30G Drawer front height 200 mm	942570 200
Storage shelf with brackets 100 kg for cabinet / compartment width in G 30	942530 30
	942570 100

Drawers for swing-door large-capacity cabinets and heavy-duty cabinets Width 30G Drawer front height 100 mm

Drawers for swing-door large-capacity cabinets and heavy-duty cabinets Width 30G Drawer front height 75 mm

942570 75

Wheels and push handle retrofit set suitable for casing depth in G 28

958480 28

Basic lighting set for GridLine cabinets with swing doors for cabinet height 900/1000 mm

940501 900/1000

Drawers for swing-door large-capacity cabinets and heavy-duty cabinets Width 30G Drawer front height 300 mm

942570 300

Drawers for swing-door large-capacity cabinets and heavy-duty cabinets Width 30G Drawer front height 150 mm

942570 150

Inclined shelf foreForm for cabinet / compartment width in G 30

942550 30

Push handle Type 1

958490 1

Drawers for swing-door large-capacity cabinets and heavy-duty cabinets Width 30G Drawer front height 125 mm

942570 125