

Garant GRIDLINE

**Large-capacity / heavy-duty cabinet with Viewing window swing door,
Height: 2000mm****Order data**

Order number	942723 2000
GTIN	4062406072674
Item class	9GI

Description**Version:**

Empty cabinet in 40×28G. Suitable drawers: 36×24G (please order these separately). Mountings for shelves at 25 mm intervals. Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves and accessories for GridLine large-capacity cabinets and heavy-duty cabinets see No. 942530 – 942610 and Group 95.

Use as a heavy-duty cabinet is only possible in conjunction with heavy load shelf No. 942610.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Depth	700 mm
Cabinet fronts	Viewing window swing door

Depth in G	28
Electronic locking system can be retrofitted	yes
Type of cabinet	Base cabinet
Handle positioning	centre
Usable height	1845 mm
ComfortClose	no
Width in G	40
Width	1000 mm
Weight	119 kg
Height	2000 mm
Version	for individual configuration
Material thickness	0.9 mm
Cabinet housing internal load capacity	1600
Door opening angle	250 degrees
Height adjustment interval	25
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Large-capacity cabinet

Accessories

Drawers for swing-door large-capacity cabinets and heavy-duty cabinets Width 40G Drawer front height 75 mm	942573 75
Drawers for swing-door large-capacity cabinets and heavy-duty cabinets Width 40G Drawer front height 100 mm	942573 100
Basic lighting set for GridLine cabinets with swing doors for cabinet height 2000 mm	940501 2000
Drawers for swing-door large-capacity cabinets and heavy-duty cabinets Width 40G Drawer front height 200 mm	942573 200

Drawers for swing-door large-capacity cabinets and heavy-duty cabinetsWidth 40G Drawer front height 125 mm	942573 125
Drawers for swing-door large-capacity cabinets and heavy-duty cabinetsWidth 40G Drawer front height 300 mm	942573 300
Extended lighting set for GridLine cabinets withSwing doors, width 40G for cabinet height 2000 mm	940511 2000
Inclined shelf foreForm for cabinet / compartment width in G 40	942550 40
Drawers for swing-door large-capacity cabinets and heavy-duty cabinetsWidth 40G Drawer front height 150 mm	942573 150
Slide handle for GridLine Type GP11	914226 GP11
Storage shelf with brackets100 kg for cabinet / compartment width in G 40	942530 40