

Garant GRIDLINE

Large-capacity / heavy-duty cabinet with Plain sheet metal sliding door, Height: 2000mm



Order data

Order number	942745 2000
GTIN	4062406072698
Item class	9GI

Description

Version:

Empty cabinet in 60×28G. Suitable drawers: 26×20G (please order these separately). Mountings for shelves at 25 mm intervals. Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves and accessories for GridLine large-capacity cabinets and heavy-duty cabinets see No. 942530 – 942610 and Group 95.

Use as a heavy-duty cabinet is only possible in conjunction with heavy load shelf No. 942610.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Electronic locking system can be retrofitted	yes
Depth in G	28

ComfortClose	no
Depth	700 mm
Usable height	1863 mm
Cabinet fronts	Plain sheet metal sliding door
Handle positioning	centre
Width	1500 mm
Width in G	60
Type of cabinet	Base cabinet
Height	2000 mm
Weight	198 kg
Version	for individual configuration
Material thickness	0.9 mm
Cabinet housing internal load capacity	1600
Height adjustment interval	25
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Large-capacity cabinet

Accessories

Lock plate for GridLine Type GP21	914227 GP21
Inclined shelf foreForm for cabinet / compartment width in G 30	942550 30
Drawers for sliding-door large-capacity cabinets and heavy-duty cabinetsWidth 30G Drawer front height 125 mm	942580 125
Drawers for sliding-door large-capacity cabinets and heavy-duty cabinetsWidth 30G Drawer front height 200 mm	942580 200
	942580 150

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets
Width 30G Drawer front height 150 mm

Extended lighting set for GridLine cabinets with Sliding doors, width 60G for cabinet height 2000 mm

940514 2000

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets
Width 30G Drawer front height 75 mm

942580 75

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets
Width 30G Drawer front height 100 mm

942580 100

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets
Width 30G Drawer front height 300 mm

942580 300

Storage shelf with brackets
100 kg for cabinet / compartment width in G 30

942530 30