

Garant GRIDLINE

Large-capacity / heavy-duty cabinet with Plain sheet metal sliding door, Height: 1000mm



Order data

| | |
|--------------|---------------|
| Order number | 942745 1000 |
| GTIN | 4062406072681 |
| Item class | 9GI |

Description

Version:

Empty cabinet in 60×28G. Suitable drawers: 26×20G (please order these separately). Mountings for shelves at 25 mm intervals. Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves and accessories for GridLine large-capacity cabinets and heavy-duty cabinets see No. 942530 – 942610 and Group 95.

Use as a heavy-duty cabinet is only possible in conjunction with heavy load shelf No. 942610.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

| | |
|----------------|--------------------------------|
| Width in G | 60 |
| Depth | 700 mm |
| Cabinet fronts | Plain sheet metal sliding door |
| Width | 1500 mm |

| | |
|--|--|
| Handle positioning | top |
| Usable height | 863 mm |
| Weight | 119 kg |
| Height | 1000 mm |
| Type of cabinet | Base cabinet |
| ComfortClose | no |
| Electronic locking system can be retrofitted | yes |
| Depth in G | 28 |
| Version | for individual configuration |
| Material thickness | 0.9 mm |
| Cabinet housing internal load capacity | 1600 |
| Height adjustment interval | 25 |
| Cylinder lock | modular barrel |
| Colour selection | RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003 |
| Type of product | Large-capacity cabinet |

Accessories

| | |
|--|------------------|
| Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 30G Drawer front height 200 mm | 942580 200 |
| Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 30G Drawer front height 300 mm | 942580 300 |
| Storage shelf with brackets 100 kg for cabinet / compartment width in G 30 | 942530 30 |
| Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 30G Drawer front height 150 mm | 942580 150 |
| Extended lighting set for GridLine cabinets with sliding doors, width 60G for cabinet height 1000/1250 mm | 940514 1000/1250 |

| | |
|--|-------------|
| Drawers for sliding-door large-capacity cabinets and heavy-duty cabinetsWidth 30G Drawer front height 100 mm | 942580 100 |
| Drawers for sliding-door large-capacity cabinets and heavy-duty cabinetsWidth 30G Drawer front height 75 mm | 942580 75 |
| Lock plate for GridLine Type GP21 | 914227 GP21 |
| Inclined shelf foreForm for cabinet / compartment width in G 30 | 942550 30 |
| Drawers for sliding-door large-capacity cabinets and heavy-duty cabinetsWidth 30G Drawer front height 125 mm | 942580 125 |