

Garant GRIDLINE

**Large-capacity / heavy-duty cabinet with Plain sheet metal sliding door,
Height: 1000mm****Order data**

Order number	942745 1000
GTIN	4062406072681
Item class	9GI

Description**Version:**

Empty cabinet in 60×28G. Suitable drawers: 26×20G (please order these separately). Mountings for shelves at 25mm intervals. Doors reinforced on the inside and can be locked by 2-component Haptoprene handle using a cylinder lock.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves and accessories for GridLine large-capacity cabinets and heavy-duty cabinets see No. 942530 – 942610 and Group 95.

Use as a heavy-duty cabinet is only possible in conjunction with heavy load shelf No. 942610.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Width in G	60
Depth	700 mm
Cabinet fronts	Plain sheet metal sliding door
Width	1500 mm

Handle positioning	top
Usable height	863 mm
Weight	119 kg
Height	1000 mm
Type of cabinet	Base cabinet
ComfortClose	no
Electronic locking system can be retrofitted	yes
Depth in G	28
Version	for individual configuration
Material thickness	0.9 mm
Cabinet housing internal load capacity	1600
Height adjustment interval	25
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Large-capacity cabinet

Accessories

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinetsWidth 30G Drawer front height 200 mm	942580 200
Drawers for sliding-door large-capacity cabinets and heavy-duty cabinetsWidth 30G Drawer front height 300 mm	942580 300
Storage shelf with brackets100 kg for cabinet / compartment width in G 30	942530 30
Drawers for sliding-door large-capacity cabinets and heavy-duty cabinetsWidth 30G Drawer front height 150 mm	942580 150
Extended lighting set for GridLine cabinets withSliding doors, width 60G for cabinet height 1000/1250 mm	940514 1000/1250

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinetsWidth 30G Drawer front height 100 mm	942580 100
Drawers for sliding-door large-capacity cabinets and heavy-duty cabinetsWidth 30G Drawer front height 75 mm	942580 75
Lock plate for GridLine Type GP21	914227 GP21
Inclined shelf foreForm for cabinet / compartment width in G 30	942550 30
Drawers for sliding-door large-capacity cabinets and heavy-duty cabinetsWidth 30G Drawer front height 125 mm	942580 125