

Garant GRIDLINE

**Large-capacity / heavy-duty cabinet with Plain sheet metal sliding door,
Height: 1000mm****Order data**

Order number	942765 1000
GTIN	4062406072728
Item class	9GI

Description**Version:**

Empty cabinet in 80×28G. Suitable drawers: 36×20G (please order these separately). Mountings for shelves at 25 mm intervals. Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves and accessories for GridLine large-capacity cabinets and heavy-duty cabinets see No. 942530 – 942610 and Group 95.

Use as a heavy-duty cabinet is only possible in conjunction with heavy load shelf No. 942610.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Handle positioning	top
Depth in G	28
Width in G	80
Electronic locking system can be retrofitted	yes
Height	1000 mm

Width	2000 mm
Cabinet fronts	Plain sheet metal sliding door
Depth	700 mm
Usable height	863 mm
Weight	138 kg
ComfortClose	no
Type of cabinet	Base cabinet
Version	for individual configuration
Material thickness	0.9 mm
Cabinet housing internal load capacity	1600
Height adjustment interval	25
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Large-capacity cabinet

Accessories

Lock plate for GridLine Type GP21	914227 GP21
Drawers for sliding-door large-capacity cabinets and heavy-duty cabinetsWidth 40G Drawer front height 100 mm	942583 100
Drawers for sliding-door large-capacity cabinets and heavy-duty cabinetsWidth 40G Drawer front height 75 mm	942583 75
Drawers for sliding-door large-capacity cabinets and heavy-duty cabinetsWidth 40G Drawer front height 300 mm	942583 300
Drawers for sliding-door large-capacity cabinets and heavy-duty cabinetsWidth 40G Drawer front height 125 mm	942583 125
Storage shelf with brackets100 kg for cabinet / compartment width in G 40	942530 40

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets
Width 40G Drawer front height 200 mm

942583 200

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets
Width 40G Drawer front height 150 mm

942583 150

Inclined shelf for cabinet / compartment width in G 40

942550 40

Extended lighting set for GridLine cabinets with sliding doors, width 80G for cabinet height 1000/1250 mm

940515 1000/1250