

Garant GRIDLINE

## Large-capacity / heavy-duty cabinet with Viewing window sliding door, Height: 1000mm



### Order data

Order number	942767 1000
GTIN	4062406072742
Item class	9GI

### Description

#### Version:

Empty cabinet in 80×28G. Suitable drawers: 36×20G (please order these separately). Mountings for shelves at 25 mm intervals. Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock.

#### Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

#### Note:

For storage shelves and accessories for GridLine large-capacity cabinets and heavy-duty cabinets see No. 942530 – 942610 and Group 95.

**Use as a heavy-duty cabinet is only possible in conjunction with heavy load shelf No. 942610.**

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

### Technical description

Depth	700 mm
Cabinet fronts	Viewing window sliding door
Width in G	80
Depth in G	28
Handle positioning	top

Width	2000 mm
Usable height	863 mm
Height	1000 mm
ComfortClose	no
Electronic locking system can be retrofitted	yes
Type of cabinet	Base cabinet
Weight	138 kg
Version	for individual configuration
Material thickness	0.9 mm
Cabinet housing internal load capacity	1600
Height adjustment interval	25
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Large-capacity cabinet

## Accessories

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 40G Drawer front height 100 mm	942583 100
Extended lighting set for GridLine cabinets with Sliding doors, width 80G for cabinet height 1000/1250 mm	940515 1000/1250
Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 40G Drawer front height 125 mm	942583 125
Storage shelf with brackets 100 kg for cabinet / compartment width in G 40	942530 40
Inclined shelf Form for cabinet / compartment width in G 40	942550 40
	942583 300

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 40G Drawer front height 300 mm

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 40G Drawer front height 150 mm

942583 150

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 40G Drawer front height 75 mm

942583 75

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 40G Drawer front height 200 mm

942583 200

Lock plate for GridLine Type GP21

914227 GP21