

Garant GRIDLINE

**Large-capacity / heavy-duty cabinet with Plain sheet metal sliding door,
Height: 2000mm****Order data**

Order number	942765 2000
GTIN	4062406072735
Item class	9GI

Description**Version:**

Empty cabinet in 80×28G. Suitable drawers: 36×20G (please order these separately). Mountings for shelves at 25 mm intervals. Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves and accessories for GridLine large-capacity cabinets and heavy-duty cabinets see No. 942530 – 942610 and Group 95.

Use as a heavy-duty cabinet is only possible in conjunction with heavy load shelf No. 942610.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Usable height	1863 mm
ComfortClose	no

Cabinet fronts	Plain sheet metal sliding door
Depth in G	28
Handle positioning	centre
Width in G	80
Depth	700 mm
Weight	225 kg
Electronic locking system can be retrofitted	yes
Type of cabinet	Base cabinet
Width	2000 mm
Height	2000 mm
Version	for individual configuration
Material thickness	0.9 mm
Cabinet housing internal load capacity	1600
Height adjustment interval	25
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Large-capacity cabinet

Accessories

Extended lighting set for GridLine cabinets with Sliding doors, width 80G for cabinet height 2000 mm	940515 2000
Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 40G Drawer front height 100 mm	942583 100
Inclined shelf foreForm for cabinet / compartment width in G 40	942550 40
Lock plate for GridLine Type GP21	914227 GP21
	942583 125

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets
Width 40G Drawer front height 125 mm

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets
Width 40G Drawer front height 75 mm

942583 75

Storage shelf with brackets
100 kg for cabinet / compartment width in G 40

942530 40

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets
Width 40G Drawer front height 300 mm

942583 300

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets
Width 40G Drawer front height 150 mm

942583 150

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets
Width 40G Drawer front height 200 mm

942583 200