

Garant GRIDLINE

## Large-capacity / heavy-duty cabinet with Viewing window sliding door, Height: 2000mm



### Order data

Order number	942767 2000
GTIN	4062406072759
Item class	9GI

### Description

#### Version:

Empty cabinet in 80×28G. Suitable drawers: 36×20G (please order these separately). Mountings for shelves at 25 mm intervals. Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock.

#### Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

#### Note:

For storage shelves and accessories for GridLine large-capacity cabinets and heavy-duty cabinets see No. 942530 – 942610 and Group 95.

**Use as a heavy-duty cabinet is only possible in conjunction with heavy load shelf No. 942610.**

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

### Technical description

Handle positioning	centre
Electronic locking system can be retrofitted	yes

Depth in G	28
Depth	700 mm
Height	2000 mm
Cabinet fronts	Viewing window sliding door
Width in G	80
Usable height	1863 mm
Weight	225 kg
Type of cabinet	Base cabinet
Width	2000 mm
ComfortClose	no
Version	for individual configuration
Material thickness	0.9 mm
Cabinet housing internal load capacity	1600
Height adjustment interval	25
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Large-capacity cabinet

## Accessories

Inclined shelf foreForm for cabinet / compartment width in G 40	942550 40
Extended lighting set for GridLine cabinets with Sliding doors, width 80G for cabinet height 2000 mm	940515 2000
Lock plate for GridLine Type GP21	914227 GP21
Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 40G Drawer front height 150 mm	942583 150
Storage shelf with brackets 100 kg for cabinet / compartment width in G 40	942530 40

