

Garant GRIDLINE

**Heavy-duty cabinet with Plain sheet metal swing door, Height: 1000 mm****Order data**

Order number	942821 1000
GTIN	4062406072803
Item class	9GI

**Description****Version:**

Empty cabinet in 40×28G. Suitable drawers: 36×24G (please order these separately).

**Reinforced side walls** to take **reinforced storage shelves for 200 kg** at 25 mm intervals.

Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. Cabinets with reinforced cabinet base, without a levelling base.

**Colour:**

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

**Note:**

For storage shelves for GridLine heavy-duty cabinets see No. 942610.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Colour selection: RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

Height: 1000 mm

Width: 1000 mm

Depth: 700 mm

Width in G: 40

Depth in G: 28

Usable height: 845 mm

**Technical description**

Width in G	40
Weight	70 kg
Depth in G	28
Depth	700 mm
Usable height	845 mm
Height	1000 mm
Width	1000 mm
Material thickness	1 mm
Cabinet housing internal load capacity	1600
Door opening angle	250 degrees
Height adjustment interval	25
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Heavy-duty cabinet, empty

## Accessories

Heavy load shelf for cabinet / compartment width in G 40	942610 40
Extended lighting set for GridLine cabinets with Swing doors, width 40G for cabinet height 1000/1250 mm	940511 1000/1250
Basic lighting set for GridLine cabinets with swing doors for cabinet height 900/1000 mm	940501 900/1000
Slide handle for GridLine Type GP11	914226 GP11