

Garant GRIDLINE

Heavy-duty cabinet with Plain sheet metal sliding door, Height: 1000 mm**Order data**

Order number	942845 1000
GTIN	4062406072841
Item class	9GI

Description**Version:**

Empty cabinet in 60×28G. Suitable drawers: 26×20G (please order these separately).

Reinforced side walls to take **reinforced storage shelves for 200 kg** at 25 mm intervals.

Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. Cabonets with reinforced cabinet base, without a levelling base.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves for GridLine heavy-duty cabinets see No. 942610.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Colour selection: RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

Height: 1000 mm

Width: 1500 mm

Depth: 700 mm

Width in G: 60

Depth in G: 28

Usable height: 845 mm

Technical description

Height	1000 mm
--------	---------

Width in G	60
Width	1500 mm
Depth in G	28
Depth	700 mm
Usable height	845 mm
Weight	119 kg
Material thickness	1 mm
Cabinet housing internal load capacity	1600
Height adjustment interval	25
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Heavy-duty cabinet, empty

Accessories

Extended lighting set for GridLine cabinets with Sliding doors, width 60G for cabinet height 1000/1250 mm	940514 1000/1250
Heavy load shelf for cabinet / compartment width in G 30	942610 30
Lock plate for GridLine Type GP21	914227 GP21
Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 30G Drawer front height 75 mm	942580 75
Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 30G Drawer front height 300 mm	942580 300
Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 30G Drawer front height 200 mm	942580 200
Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 30G Drawer front height 150 mm	942580 150
	942580 125

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 30G Drawer front height 125 mm

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 30G Drawer front height 100 mm

942580 100