

Garant GRIDLINE

**Heavy-duty cabinet with Viewing window sliding door, Height: 2000 mm****Order data**

Order number	942847 2000
GTIN	4062406072872
Item class	9GI

**Description****Version:**

Empty cabinet in 60×28G. Suitable drawers: 26×20G (please order these separately).

**Reinforced side walls** to take **reinforced storage shelves for 200 kg** at 25 mm intervals.

Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. Cabinets with reinforced cabinet base, without a levelling base.

**Colour:**

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

**Note:**

For storage shelves for GridLine heavy-duty cabinets see No. 942610.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Colour selection: RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

Height: 2000 mm

Width: 1500 mm

Depth: 700 mm

Width in G: 60

Depth in G: 28

Usable height: 1845 mm

**Technical description**

Depth	700 mm
Usable height	1845 mm
Height	2000 mm
Width in G	60
Weight	198 kg
Width	1500 mm
Depth in G	28
Material thickness	1 mm
Cabinet housing internal load capacity	1600
Height adjustment interval	25
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Heavy-duty cabinet, empty

## Accessories

Heavy load shelf for cabinet / compartment width in G 30	942610 30
Extended lighting set for GridLine cabinets with Sliding doors, width 60G for cabinet height 2000 mm	940514 2000
Lock plate for GridLine Type GP21	914227 GP21
Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 30G Drawer front height 75 mm	942580 75
Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 30G Drawer front height 300 mm	942580 300
Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 30G Drawer front height 200 mm	942580 200
	942580 150

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 30G Drawer front height 150 mm

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 30G Drawer front height 125 mm

942580 125

Drawers for sliding-door large-capacity cabinets and heavy-duty cabinets Width 30G Drawer front height 100 mm

942580 100