

Garant GRIDLINE

Heavy-duty cabinet with Viewing window sliding door, Height: 1000 mm



Order data

Order number	942867 1000
GTIN	4062406072902
Item class	9GI

Description

Version:

Empty cabinet in 80×28G. Suitable drawers: 36×20G (please order these separately).

Reinforced side walls to take **reinforced storage shelves for 200 kg** at 25 mm intervals.

Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. Cabinets with reinforced cabinet base, without a levelling base.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves for GridLine heavy-duty cabinets see No. 942610.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Colour selection: RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

Height: 1000 mm

Width: 2000 mm

Depth: 700 mm

Width in G: 80

Depth in G: 28

Usable height: 845 mm

Technical description

Height	1000 mm
Depth in G	28

Width in G	80
Usable height	845 mm
Width	2000 mm
Weight	138 kg
Depth	700 mm
Material thickness	1 mm
Cabinet housing internal load capacity	1600
Height adjustment interval	25
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Heavy-duty cabinet, empty

Accessories

Extended lighting set for GridLine cabinets with Sliding doors, width 80G for cabinet height 1000/1250 mm	940515 1000/1250
Heavy load shelf for cabinet / compartment width in G 40	942610 40
Lock plate for GridLine Type GP21	914227 GP21