

Garant GRIDLINE

Heavy-duty cabinet with Viewing window sliding door, Height: 2000 mm



Order data

| | |
|--------------|---------------|
| Order number | 942867 2000 |
| GTIN | 4062406072919 |
| Item class | 9GI |

Description

Version:

Empty cabinet in 80×28G. Suitable drawers: 36×20G (please order these separately).

Reinforced side walls to take **reinforced storage shelves for 200 kg** at 25 mm intervals.

Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. Cabinets with reinforced cabinet base, without a levelling base.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves for GridLine heavy-duty cabinets see No. 942610.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Colour selection: RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

Height: 2000 mm

Width: 2000 mm

Depth: 700 mm

Width in G: 80

Depth in G: 28

Usable height: 1845 mm

Technical description

| | |
|--|--|
| Depth | 700 mm |
| Weight | 225 kg |
| Width | 2000 mm |
| Usable height | 1845 mm |
| Depth in G | 28 |
| Width in G | 80 |
| Height | 2000 mm |
| Material thickness | 1 mm |
| Cabinet housing internal load capacity | 1600 |
| Height adjustment interval | 25 |
| Cylinder lock | modular lock barrel |
| Colour selection | RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003 |
| Type of product | Heavy-duty cabinet, empty |

Accessories

| | |
|--|-------------|
| Heavy load shelf for cabinet / compartment width in G 40 | 942610 40 |
| Extended lighting set for GridLine cabinets with Sliding doors, width 80G for cabinet height 2000 mm | 940515 2000 |
| Lock plate for GridLine Type GP21 | 914227 GP21 |