

Garant**Garment locker with rotary catch, Number of compartments: 3****Order data**

Order number	949012 3
GTIN	4062406073060
Item class	91G

Description**Version:**

Feet of 2 mm thick aluminium sheet. Back walls with ventilation slots, doors with towel holder and name plate. The door can easily be converted from right- to left-hinged.

With rotary catch; lockable with a padlock (not included in delivery).

Each fitted internally with 1 storage shelf (load capacity 40 kg).

Hanger rail with 3 hooks per compartment.

Standard:**DIN 4547****Colour:**

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

Optionally with a plinth panel. Please contact us.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Height	1850 mm
--------	---------

Standard	DIN 4547
Nameplate	yes
for padlock	yes
Support cabinet version	Aluminium feet
Number of clothes rails	1
Ventilation slots in the back wall	yes
Ventilation slots in the door	no
usable height of each hat compartment	370 mm
Sloping roof	no
usable depth of each compartment	472 mm
suitable for integral helmets	yes
Width	1200 mm
Depth	520 mm
usable height of each clothing compartment	1188 mm
Cabinet fronts	Plain sheet metal swing door
Special paints available	yes
Lock version	Rotary catch
Weight	102 kg
Number of fixed shelves	1
usable width of each compartment	342 mm
for padlock with shackle Ø up to	6 mm
Number of compartments	3
Material thickness	0.9 mm
Door opening angle	225 degrees
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Locker

Accessories

Base fascia, front Type 1200	958737 1200
Precision cylinder padlockwith lock barrel, individual keys Body Ø 45 mm	085814 45
Precision cylinder padlockwithout lock barrel Body Ø 45 mm	085816 45
Precision cylinder lock with high shackleindividual keys Body Ø 40 mm	085875 40
Rotary catch Type R	914190 R
Base fascia side Type 520	958738 520
Precision cylinder padlockwith lock barrel, shared key Body Ø 45 mm	085812 45