

**Garant****Garment locker with rotary catch, Number of compartments: 2****Order data**

Order number	949012 2
GTIN	4062406073053
Item class	91G

**Description****Version:**

Feet of 2 mm thick aluminium sheet. Back walls with ventilation slots, doors with towel holder and name plate. The door can easily be converted from right- to left-hinged.

With rotary catch; lockable with a padlock (not included in delivery).

Each fitted internally with 1 storage shelf (load capacity 40 kg).

Hanger rail with 3 hooks per compartment.

**Standard:****DIN 4547****Colour:**

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

**Note:**

Optionally with a plinth panel. Please contact us.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

**Technical description**

usable depth of each compartment	472 mm
----------------------------------	--------

Number of compartments	2
Number of fixed shelves	1
Weight	68 kg
Depth	520 mm
usable width of each compartment	342 mm
Ventilation slots in the back wall	yes
for padlock with shackle Ø up to	6 mm
for padlock	yes
Support cabinet version	Aluminium feet
Lock version	Rotary catch
Width	800 mm
Height	1850 mm
Special paints available	yes
Cabinet fronts	Plain sheet metal swing door
Number of clothes rails	1
Sloping roof	no
usable height of each clothing compartment	1188 mm
Ventilation slots in the door	no
Nameplate	yes
usable height of each hat compartment	370 mm
Standard	DIN 4547
suitable for integral helmets	yes
Material thickness	0.9 mm
Door opening angle	225 degrees
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Locker

## Accessories

Base fascia side Type 520	958738 520
Rotary catch Type R	914190 R
Precision cylinder padlockwithout lock barrel Body Ø 45 mm	085816 45
Precision cylinder padlockwith lock barrel, individual keys Body Ø 45 mm	085814 45
Precision cylinder padlockwith lock barrel, shared key Body Ø 45 mm	085812 45
Base fascia, front Type 800	958737 800
Precision cylinder lock with high shackleindividual keys Body Ø 40 mm	085875 40