

Garant**Garment locker with rotary catch, Number of compartments: 4****Order data**

Order number	949015 4
GTIN	4062406073091
Item class	91G

Description**Version:**

Feet of 2 mm thick aluminium sheet. Back walls with ventilation slots, doors with towel holder and name plate. The door can easily be converted from right- to left-hinged.

With rotary catch; lockable with a padlock (not included in delivery).

Hanger rail with 3 hooks per compartment.

Standard:

DIN 4547

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

Optionally with a plinth panel. Please contact us.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Cabinet fronts	Plain sheet metal swing door
Special paints available	yes

Standard	DIN 4547
Support cabinet version	Aluminium feet
Weight	68 kg
suitable for integral helmets	yes
Number of compartments	4
for padlock with shackle Ø up to	6 mm
Sloping roof	no
Ventilation slots in the door	no
Nameplate	yes
usable depth of each compartment	472 mm
Depth	520 mm
Width	800 mm
Number of clothes rails	1
usable height of each compartment	780 mm
Ventilation slots in the back wall	yes
usable width of each compartment	342 mm
Height	1850 mm
for padlock	yes
Lock version	Rotary catch
Material thickness	0.9 mm
Door opening angle	225 degrees
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Locker

Accessories

Precision cylinder padlock with lock barrel, individual keys
Body Ø 45 mm

085814 45

Precision cylinder padlock with lock barrel, shared key Body Ø 45 mm	085812 45
Precision cylinder lock with high shackle individual keys Body Ø 40 mm	085875 40
Base fascia side Type 520	958738 520
Base fascia, front Type 800	958737 800
Precision cylinder padlock without lock barrel Body Ø 45 mm	085816 45
Rotary catch Type R	914190 R