

Garant**Garment locker with rotary catch, Number of compartments: 8****Order data**

Order number	949018 8
GTIN	4062406073138
Item class	91G

Description**Version:**

Feet of 2 mm thick aluminium sheet. Back walls with ventilation slots, doors with towel holder and name plate. The door can easily be converted from right- to left-hinged.

With rotary catch; lockable with a padlock (not included in delivery).

Standard:**DIN 4547****Colour:**

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

Optionally with a plinth panel. Please contact us.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Standard	DIN 4547
for padlock with shackle Ø up to	6 mm

Support cabinet version	Aluminium feet
Height	1850 mm
usable width of each compartment	342 mm
Width	800 mm
Ventilation slots in the back wall	yes
Lock version	Rotary catch
Nameplate	yes
usable depth of each compartment	472 mm
usable height of each compartment	370 mm
Depth	520 mm
Sloping roof	no
Number of compartments	8
Weight	76 kg
for padlock	yes
Special paints available	yes
Cabinet fronts	Plain sheet metal swing door
Material thickness	0.9 mm
Door opening angle	225 degrees
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Storage cabinet

Accessories

Rotary catch Type R	914190 R
Precision cylinder padlockwith lock barrel, individual keys Body Ø 45 mm	085814 45
Precision cylinder padlockwith lock barrel, shared key Body Ø 45 mm	085812 45
	085875 40

Precision cylinder lock with high shackle individual keys
Body Ø 40 mm

Base fascia, front Type 800

958737 800

Precision cylinder padlock without lock barrel Body Ø 45
mm

085816 45

Base fascia side Type 520

958738 520