

**Garant****Garment locker with rotary catch, Number of compartments: 12****Order data**

Order number	949018 12
GTIN	4062406073145
Item class	91G

**Description****Version:**

Feet of 2 mm thick aluminium sheet. Back walls with ventilation slots, doors with towel holder and name plate. The door can easily be converted from right- to left-hinged.

With rotary catch; lockable with a padlock (not included in delivery).

**Standard:****DIN 4547****Colour:**

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

**Note:**

Optionally with a plinth panel. Please contact us.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

**Technical description**

Weight	114 kg
for padlock with shackle Ø up to	6 mm

Special paints available	yes
usable depth of each compartment	472 mm
Ventilation slots in the back wall	yes
usable width of each compartment	342 mm
Height	1850 mm
for padlock	yes
Lock version	Rotary catch
Number of compartments	12
Depth	520 mm
Support cabinet version	Aluminium feet
usable height of each compartment	370 mm
Width	1200 mm
Cabinet fronts	Plain sheet metal swing door
Nameplate	yes
Standard	DIN 4547
Sloping roof	no
Material thickness	0.9 mm
Door opening angle	225 degrees
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Storage cabinet

## Accessories

Precision cylinder padlock with lock barrel, shared key Body Ø 45 mm	085812 45
Base fascia, front Type 1200	958737 1200
Precision cylinder lock with high shackle individual keys Body Ø 40 mm	085875 40
	085814 45

Precision cylinder padlockwith lock barrel, individual keys  
Body Ø 45 mm

Rotary catch Type R

914190 R

Base fascia side Type 520

958738 520

Precision cylinder padlockwithout lock barrel Body Ø 45  
mm

085816 45