

**Garant****Garment locker with rotary catch, Number of compartments: 2****Order data**

Order number	949051 2
GTIN	4062406073176
Item class	91G

**Description****Version:**

Doors with resilient stops. The body has a **sloping top**, plastic slides for the shelf assembly and a **removable plinth panel** at the front. One storage shelf with 2 clothes hooks per compartment. The special construction enables storage of integral helmets, despite a unit width of only 300 mm (design registration applied for).

With rotary catch; up to size 40 can be locked with padlock (not included).

**Standard:**

**DIN 4547**

**Colour:**

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

**Note:**

- **Lockers are supplied fully assembled.**
- **For padlocks for the rotary catch see catalogue volume 2 Hand tools and Metrology No. 085822–085890, and also DOM padlock No. 085812; 085814. No. 085816 size 45.**
- **Suitable for locking systems.**

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

**Technical description**

Height at the rear	2000 mm
usable height of each hat compartment with sloping roof	420 - 480 mm
for padlock	yes
usable depth of each hat compartment	250 mm
for padlock with shackle Ø up to	6 mm
usable height of each clothing compartment	1240 mm
usable width of each clothing compartment	240 mm
Storage shelf depth	250 mm
usable width of each hat compartment (integral helmet)	240 - 280 mm
Sloping roof	yes
Weight	49.8 kg
Ventilation slots in the back wall	no
Nameplate	yes
Lock version	Rotary catch
Height at the front	1850 mm
Width	600 mm
Shelf width	295 mm
Standard	DIN 4547
usable depth of each clothing compartment	475 mm
Support cabinet version	Base with base fascia
Ventilation slots in the door	no
Base fascia removable	yes
Number of compartments	2
Number of clothes rails	1
Cabinet fronts	Plain sheet metal swing door
Special paints available	yes
Depth	500 mm
Number of fixed shelves	1
suitable for integral helmets	yes

Material thickness	0.8 mm
Door opening angle	225 degrees
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Locker

## Accessories

Rotary catch Type R	914190 R
Precision cylinder padlockwith lock barrel, shared key Body Ø 45 mm	085812 45
Precision cylinder padlockwithout lock barrel Body Ø 45 mm	085816 45
Precision cylinder padlockwith lock barrel, individual keys Body Ø 45 mm	085814 45
Precision cylinder lock with high shackleindividual keys Body Ø 40 mm	085875 40