

Garant**Garment locker with rotary catch, Number of compartments: 3****Order data**

Order number	949051 3
GTIN	4062406073183
Item class	91G

Description**Version:**

Doors with resilient stops. The body has a **sloping top**, plastic slides for the shelf assembly and a **removable plinth panel** at the front. One storage shelf with 2 clothes hooks per compartment. The special construction enables storage of integral helmets, despite a unit width of only 300 mm (design registration applied for).

With rotary catch; up to size 40 can be locked with padlock (not included).

Standard:

DIN 4547

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

- **Lockers are supplied fully assembled.**
- **Padlocks for the rotary catch No. 085822–085890, and also DOM padlock No. 085812; 085814. No. 085816 size 45.**
- **Suitable for locking systems.**

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

usable height of each clothing compartment	1240 mm
usable width of each hat compartment (integral helmet)	240 - 280 mm
Base fascia removable	yes
Height at the front	1850 mm
Number of fixed shelves	1
Lock version	Rotary catch
for padlock with shackle Ø up to	6 mm
Ventilation slots in the back wall	no
usable width of each clothing compartment	240 mm
Depth	500 mm
Number of compartments	3
Ventilation slots in the door	no
Width	900 mm
Support cabinet version	Base with base fascia
Height at the rear	2000 mm
usable height of each hat compartment with sloping roof	420 - 480 mm
Special paints available	yes
Shelf width	295 mm
usable depth of each hat compartment	250 mm
Standard	DIN 4547
Cabinet fronts	Plain sheet metal swing door
suitable for integral helmets	yes
usable depth of each clothing compartment	475 mm
Nameplate	yes
Weight	69.3 kg
Storage shelf depth	250 mm
Number of clothes rails	1
Sloping roof	yes
for padlock	yes

Material thickness	0.8 mm
Door opening angle	225 degrees
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Locker

Accessories

Precision cylinder padlockwith lock barrel, shared key Body Ø 45 mm	085812 45
Precision cylinder padlockwith lock barrel, individual keys Body Ø 45 mm	085814 45
Precision cylinder padlockwithout lock barrel Body Ø 45 mm	085816 45
Precision cylinder lock with high shackleindividual keys Body Ø 40 mm	085875 40
Rotary catch Type R	914190 R