

Garant GRIDLINE

Garment lockers with cylinder lock, Number of compartments: 4



Order data

Order number	949073 4
GTIN	4062406073206
Item class	9GF

Description

Version:

Doors with resilient stops. Plastic slides in the base frame. Base frame height 80 mm. Top frame height 40 mm. Top and base flush with the door. Fitted swing doors. The door can easily be converted from right- to left-hinged. With high quality cylinder lock in the slide handle. Internal fitments: Clothes hook strip with 3 hooks, fitted directly under the top board of the compartment.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Colour selection: RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

Height: 2000 mm

Width: 800 mm

Depth: 500 mm

Width in G: 32

Depth in G: 20

usable height of each compartment: 900 mm

Technical description

usable depth of each clothing compartment	450 mm
usable height of each clothing compartment	900 mm
Depth	500 mm
usable height of each compartment	900 mm
Sloping roof	no
Special paints available	yes
Lock version	Cylinder lock
Width	800 mm
Support cabinet version	Fitted base
Ventilation slots in the door	no
Ventilation slots in the back wall	yes
Cabinet fronts	Plain sheet metal swing door
Number of clothes rails	1
Standard	DIN 4547
Base fascia removable	no
Number of compartments	4
usable width of each clothing compartment	340 mm
Weight	81.5 kg
Height	2000 mm
suitable for integral helmets	yes
Width in G	32
Depth in G	20
Material thickness	0.9 mm
Door opening angle	250 degrees
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Locker

Accessories

Slide handle for garment lockers without cylinder insert	914221
Slide handle for GridLine Type GP12	914226 GP12