

Garant GRIDLINE

**Garment lockers with cylinder lock, Number of compartments: 2****Order data**

Order number	949071 2
GTIN	4062406073190
Item class	9GF

**Description****Version:**

Doors with resilient stops. Plastic slides in the base frame. Base frame height 80 mm. Top frame height 40 mm. Top and base flush with the door. Fitted swing doors. The door can easily be converted from right- to left-hinged. With high quality cylinder lock in the slide handle. Internal fittings: With 1 shelf and 3 clothes hooks.

**Colour:**

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

**Note:**

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Colour selection: RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

Height: 2000 mm

Width: 800 mm

Depth: 500 mm

Width in G: 32

Depth in G: 20

usable height of each compartment: 1840 mm

**Technical description**

usable depth of each hat compartment	450 mm
suitable for integral helmets	yes
Height	2000 mm
usable width of each hat compartment	340 mm
Ventilation slots in the back wall	yes
Cabinet fronts	Plain sheet metal swing door
Lock version	Cylinder lock
usable height of each compartment	1840 mm
Sloping roof	no
Weight	85.3 kg
Base fascia removable	no
Number of fixed shelves	1
usable width of each clothing compartment	340 mm
Number of clothes rails	1
Ventilation slots in the door	no
usable depth of each clothing compartment	450 mm
usable height of each clothing compartment	1430 mm
usable height of each hat compartment	370 mm
Standard	DIN 4547
Special paints available	yes
Depth	500 mm
Width	800 mm
Support cabinet version	Fitted base
Number of compartments	2
Width in G	32
Depth in G	20
Material thickness	0.9 mm
Door opening angle	250 degrees
Cylinder lock	modular barrel

Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Locker

---

## Accessories

Slide handle for garment lockers without cylinder insert	914221
Slide handle for GridLine Type GP12	914226 GP12