

Garant**Shelving cabinet with plain sheet metal swing doors, Height: 1000mm****Order data**

Order number	944003 1000
GTIN	4062406073381
Item class	9GI

Description**Version:**

Equipped shelf cabinet in 30×11G.

Mountings for storage shelves at 25-mm intervals.

Doors reinforced on the inside and can be locked by 2-component Haptoprene® push handle using a cylinder lock.

Fitted with:

Number of storage bins: 12 × No. 963321 size SB6; 12 × No. 963321 size SB5; 12 × No. 963321 size SB4

Supplied with:

Cabinet with shelves and open storage bins.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

- **For single open storage bins see No 963321.**
- **For individual storage shelves see No. 944061, 944065.**

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Usable height	845 mm
Shelf load capacity / maximum distributed shelf load (on metal)	80 kg
Weight	47 kg
Width	750 mm
Height	1000 mm
Cabinet fronts	Plain sheet metal swing door
Number of shelves	4
Depth	275 mm
Depth in G	11
Width in G	30
Material thickness	0.9 mm
Cabinet housing internal load capacity	500 kg
Door opening angle	250 degrees
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Racking cupboard

Accessories

Shelf clip set for GridLine cabinets 20 pieces Type F	940559 F
Slide handle for GridLine Type GP11	914226 GP11
Stepped shelves for shelving cabinets, depth 11 G for cabinet width in G 30	944065 30
Storage shelves for shelving cabinets, depth 11 G for cabinet width in G 30	944061 30