

Garant GRIDLINE

Modular shelving cabinet with plain sheet metal swing doors equipped with storage bins, Height: 2000mm



Order data

Order number	944221 2000
GTIN	4062406073503
Item class	9GI

Description

Version:

Equipped shelf cabinet in 40×20G. Mountings for shelves at 25 mm intervals. Can be locked by 2-component Haptoprene® push handle using a cylinder lock. Plain sheet metal swing doors with rack panels to take open storage bins and Easyfix hooks and supports. Fitted with storage shelves and open storage bins.

6 pcs. storage shelves with **65 kg load capacity**.

3 pcs. storage shelves with **100 kg load capacity**.

Fitted with:

Number of storage bins: 36 × No. 963321 size SB6; 51 × No. 963321 size SB5; 18 × No. 963321 size SB4; 16 × No. 963321 size SB3Z

Supplied with:

Cabinet with shelves and open storage bins.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

Load capacity per door: 8 kg.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Usable height	1845 mm
Weight	151 kg
Height	2000 mm
Cabinet fronts	Plain sheet metal swing door
Number of shelves	9
Depth	500 mm
Width	1000 mm
Depth in G	20
Width in G	40
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Door opening angle	250 degrees
Hoffmann perforated panel grid interval	9×9 mm
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Racking cupboard

Accessories

Shelf clip set for GridLine cabinets 20 pieces Type F	940559 F
Slide handle for GridLine Type GP11	914226 GP11