

Garant GRIDLINE

Battery charging cabinet with plain sheet metal swing doors, Height: 1000/DEmm**Order data**

Order number	944501 1000/DE
GTIN	4062406073534
Item class	9GI

Description**Version:**

Equipped battery charging cabinet in 40×20G, with **earth leak trip fuse box** and **fan**. Fan with air filter in overpressure operation (50 m³ / h). Air escapes through horizontal ventilation slots in the doors. Battery charging shelves each with two 6-way 230 V socket strips with ON/OFF switch.

Supplied with:

Cabinet supplied with 2 perforated battery charging shelves. Connection plug 16 A / 400 V 5-pin with 3 m cable and **measurement certificate**. 4 × 6-way socket strip.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

German socket version.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Number of sockets	24
Weight	88 kg
Usable height	845 mm
Height	1000 mm

Depth	500 mm
Width	1000 mm
Width in G	40
Depth in G	20
Power supply	Mains operated
Plug type, input	F
On/Off switch	yes
Nominal voltage	400 V
Number of sockets type F	24
Socket type	F
Material thickness	0.9 mm
Door opening angle	250 degrees
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Battery charging cabinet

Accessories

Slide handle for GridLine Type GP11	914226 GP11
-------------------------------------	-------------