

Garant GRIDLINE

Battery charging cabinet with Viewing window swing doors, Height: 1250/DEmm**Order data**

Order number	944503 1250/DE
GTIN	4062406073572
Item class	9GI

Description**Version:**

Equipped battery charging cabinet in 40×20G, with **earth leak trip fuse box** and **fan**. Fan with air filter in overpressure operation (50 m³ / h). Air escapes through horizontal ventilation slots in the doors. Battery charging shelves each with two 6-way 230 V socket strips with ON/OFF switch.

Supplied with:

Cabinet supplied with 2 perforated battery charging shelves. Connection plug 16 A / 400 V 5-pin with 3 m cable and **measurement certificate**. 4 × 6-way socket strip.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

German socket version.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Weight	95 kg
Width	1000 mm
Height	1250 mm

Usable height	1095 mm
Depth	500 mm
Number of sockets	24
Width in G	40
Depth in G	20
Power supply	Mains operated
On/Off switch	yes
Plug type, input	F
Nominal voltage	400 V
Number of sockets type F	24
Socket type	F
Material thickness	0.9 mm
Door opening angle	250 degrees
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Battery charging cabinet

Accessories

Slide handle for GridLine Type GP11	914226 GP11
-------------------------------------	-------------