

Garant GRIDLINE

Computer terminal, Type: GB**Order data**

Order number	948101 GB
GTIN	4062406073640
Item class	9GS

Description**Version:**

TFT monitor housing for flat screen. Storage shelf made of bamboo. Computer housing fitted with fan and an adjustable galvanised storage shelf.

Function:

IP41: Protected against water falling vertically and protected against penetration by foreign bodies with $\varnothing > 1$ mm, however tools and wires should be kept away.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Footrests are **always** RAL 7016 anthracite grey **powder-coated**.

Note:

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Height	1620 mm
Depth	500 mm
Monitor housing usable height	460 mm

Width	750 mm
Weight	73 kg
Monitor housing usable width	690 mm
Depth in G	20
Monitor housing usable depth	230 mm
Width in G	30
Support cabinet usable height	845 mm
Support cabinet usable width	700 mm
IP Index of Protection	IP 41
Power supply	Mains operated
Nominal voltage	250 V
On/Off switch	yes
Plug type, input	G
Material thickness	0.9 mm
Door opening angle	250 degrees
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Computer desk

Accessories

Slide handle for GridLine Type GP11	914226 GP11
Slide handle for garment lockers without cylinder insert	914221