

Garant GRIDLINE

**Computer terminal, Type: FR****Order data**

Order number	948101 FR
GTIN	4062406073633
Item class	9GS

**Description****Version:**

TFT monitor housing for flat screen. Storage shelf made of bamboo. Computer housing fitted with fan and an adjustable galvanised storage shelf.

**Function:**

IP41: Protected against water falling vertically and protected against penetration by foreign bodies with  $\varnothing > 1$  mm, however tools and wires should be kept away.

**Colour:**

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Footrests are **always** RAL 7016 anthracite grey **powder-coated**.

**Note:**

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

**Technical description**

Depth	500 mm
Weight	73 kg
Monitor housing usable width	690 mm

Width in G	30
Depth in G	20
Monitor housing usable depth	230 mm
Width	750 mm
Monitor housing usable height	460 mm
Height	1620 mm
Support cabinet usable height	845 mm
Support cabinet usable width	700 mm
IP Index of Protection	IP 41
Power supply	Mains operated
Nominal voltage	250 V
Plug type, input	E
On/Off switch	yes
Material thickness	0.9 mm
Door opening angle	250 degrees
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Computer desk

## Accessories

Slide handle for garment lockers without cylinder insert	914221
Slide handle for GridLine Type GP11	914226 GP11