

Garant GRIDLINE

Computer terminal, Type: IT**Order data**

| | |
|--------------|---------------|
| Order number | 948111 IT |
| GTIN | 4062406073688 |
| Item class | 9GS |

Description**Version:**

Monitor housing with fan for CRT monitors up to 19 inches. Swing door with polycarbonate window, lockable.

Keyboard drawer locks in full travel position. Three height adjustments at 60 mm intervals (1058 / 1118 / 1178 mm), can be locked, with palm rest of bamboo and cable strain relief.

Computer housing with fan and 1 height-adjustable galvanised shelf, and cable slots for a tidy cable layout. One key for all locks.

Function:

IP41: Protected against water falling vertically and protected against penetration by foreign bodies with $\varnothing > 1$ mm, however tools and wires should be kept away.

Colour:

Body RAL 7035 light grey, doors and drawer front RAL 7016 anthracite **powder-coated**.

Note:

The dimensions of the computer workstation are compatible with GridLine cabinets depth 20G No. 940001 – 940217, 940801 – 940907 and can be combined with them as required.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

| | |
|---|--|
| Monitor housing usable width | 690 mm |
| maximum screen size, diagonal | 19 in |
| Height | 2000 mm |
| Depth | 500 mm |
| Computer housing usable depth | 470 mm |
| Viewing window height | 532 mm |
| Monitor housing usable height | 570 mm |
| Viewing window width | 552 mm |
| Depth in G | 20 |
| Computer housing usable height | 845 mm |
| Width in G | 30 |
| Weight | 77 kg |
| Computer housing usable width | 700 mm |
| Monitor housing usable depth | 458 mm |
| Width | 750 mm |
| Shelf load capacity / maximum distributed shelf load (on metal) | 100 kg |
| IP Index of Protection | IP 41 |
| Power supply | Mains operated |
| Plug type, input | L |
| On/Off switch | yes |
| Nominal voltage | 250 V |
| Material thickness | 0.9 mm |
| Door opening angle | 250 degrees |
| Cylinder lock | modular barrel |
| Colour selection | RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003 |
| Type of product | Computer workstation |

Accessories

| | |
|--|-------------|
| Slide handle for GridLine Type GP11 | 914226 GP11 |
| Slide handle for garment lockers without cylinder insert | 914221 |