

Garant GRIDLINE

Computer workstation, Type: FR**Order data**

| | |
|--------------|---------------|
| Order number | 948121 FR |
| GTIN | 4062406073817 |
| Item class | 9GS |

Description**Version:**

TFT monitor housing for flat screens, with fixed storage compartment for cables. Computer housing with fan in the housing cover and an adjustable shelf. Lockable keyboard drawer with palm rest of bamboo, height adjustable in 3 steps at 60-mm spacing. Keyboard drawer locks in full travel position. Storage shelf made of bamboo.

Function:

IP41: Protected against water falling vertically and protected against penetration by foreign bodies with $\varnothing > 1$ mm, however tools and wires should be kept away.

Colour:

Body RAL 7035 light grey, doors and drawers RAL 7016 anthracite **powder-coated**.

Note:

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

| | |
|--------|--------|
| Weight | 82 kg |
| Width | 750 mm |

| | |
|-------------------------------|--|
| Depth | 500 mm |
| Width in G | 30 |
| Monitor housing usable depth | 230 mm |
| Depth in G | 20 |
| Monitor housing usable width | 690 mm |
| Height | 1740 mm |
| Monitor housing usable height | 460 mm |
| Support cabinet usable width | 700 mm |
| Support cabinet usable height | 645 mm |
| IP Index of Protection | IP 41 |
| Power supply | Mains operated |
| Nominal voltage | 250 V |
| Plug type, input | E |
| On/Off switch | yes |
| Material thickness | 0.9 mm |
| Door opening angle | 250 degrees |
| Cylinder lock | modular barrel |
| Colour selection | RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003 |
| Type of product | Computer workstation |

Accessories

| | |
|--|-------------|
| Slide handle for GridLine Type GP11 | 914226 GP11 |
| Slide handle for garment lockers without cylinder insert | 914221 |