

Garant GRIDLINE

Computer workstation mobile, Type: DE



Order data

Order number	948141 DE
GTIN	4062406073961
Item class	9GS

Description

Version:

The **keyboard drawer** snaps into place in full travel position, can be locked. With bamboo palm rest and cable strain relief. Top extension with keyboard drawer with perforated panel at side □ 9×9 mm at 37 mm intervals for mounting Easyfix hooks and holders. **Computer housing** with **fan**, adjustable galvanised storage shelf and fixed storage shelf of bamboo.

With mobile base composed of 2 fixed wheels and 2 electrically conductive castors with brakes Ø 125 mm and push handles.

Function:

IP41: Protected against water falling vertically and protected against penetration by foreign bodies with Ø > 1 mm, however tools and wires should be kept away.

Supplied with:

The integral **electrical installation** includes a multiple socket outlet (6-way 250 V/16 A with ON/OFF switch), connection cable 1.2 m.

Colour:

Body RAL 7035 light grey, doors and drawers RAL 7016 anthracite **powder-coated**.

Technical description

Width in G	30
------------	----

Width	750 mm
Height	1170 mm
Weight	69 kg
Depth in G	20
Depth	500 mm
Support cabinet usable height	645 mm
Support cabinet usable width	700 mm
IP Index of Protection	IP 41
On/Off switch	yes
Nominal voltage	250 V
Plug type, input	F
Material thickness	0.9 mm
Door opening angle	250 degrees
Hoffmann perforated panel grid interval	9×9 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Computer workstation

Accessories

Slide handle for GridLine Type GP11	914226 GP11
-------------------------------------	-------------