

Garant GRIDLINE

**Computer workstation with printer flap, Type: FR****Order data**

Order number	948132 FR
GTIN	4062406074050
Item class	9GS

**Description****Version:**

The **keyboard drawer** snaps into place in full travel position, can be locked. With bamboo palm rest and cable strain relief. Top extension with keyboard drawer with perforated panel at side □ 9×9 mm at 37 mm intervals for mounting Easyfix hooks and holders. **Computer housing** with **fan**, adjustable galvanised storage shelf and fixed storage shelf of bamboo.

**Function:**

IP41: Protected against water falling vertically and protected against penetration by foreign bodies with  $\varnothing > 1$  mm, however tools and wires should be kept away.

**Colour:**

Body RAL 7035 light grey, doors and drawers RAL 7016 anthracite **powder-coated**.

**Note:**

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

**Technical description**

Width	750 mm
Width in G	30

Height	1020 mm
Dimensions printer flap	236×290 mm
Depth	500 mm
Depth in G	20
Weight	69 kg
Support cabinet usable width	700 mm
Support cabinet usable height	645 mm
IP Index of Protection	IP 41
Power supply	Mains operated
On/Off switch	yes
Plug type, input	E
Nominal voltage	250 V
Material thickness	0.9 mm
Door opening angle	250 degrees
Hoffmann perforated panel grid interval	9×9 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Computer workstation

---

## Accessories

Slide handle for GridLine Type GP11	914226 GP11
-------------------------------------	-------------