

Garant GRIDLINE

Computer workstation with printer flap, Type: DE**Order data**

Order number	948132 DE
GTIN	4062406074029
Item class	9GS

Description**Version:**

The **keyboard drawer** snaps into place in full travel position, can be locked. With bamboo palm rest and cable strain relief. Top extension with keyboard drawer with perforated panel at side □ 9×9 mm at 37 mm intervals for mounting Easyfix hooks and holders. **Computer housing** with **fan**, adjustable galvanised storage shelf and fixed storage shelf of bamboo.

Function:

IP41: Protected against water falling vertically and protected against penetration by foreign bodies with $\varnothing > 1$ mm, however tools and wires should be kept away.

Supplied with:

The integral **electrical installation** includes a multiple socket outlet (6-way 250 V/16 A with ON/OFF switch), connection cable 1.2 m.

Colour:

Body RAL 7035 light grey, doors and drawers RAL 7016 anthracite **powder-coated**.

Note:

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Weight	69 kg
Height	1020 mm
Width	750 mm
Depth in G	20
Width in G	30
Depth	500 mm
Dimensions printer flap	236×290 mm
Support cabinet usable height	645 mm
Support cabinet usable width	700 mm
IP Index of Protection	IP 41
Power supply	Mains operated
On/Off switch	yes
Plug type, input	F
Nominal voltage	250 V
Material thickness	0.9 mm
Door opening angle	250 degrees
Hoffmann perforated panel grid interval	9×9 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Computer workstation

Accessories

Slide handle for GridLine Type GP11	914226 GP11
-------------------------------------	-------------