

Garant GRIDLINE

**Computer workstation, Type: IT****Order data**

Order number	948201 IT
GTIN	4062406074173
Item class	9GS

**Description****Version:**

Computer cabinet with separately lockable double-leaf door with polycarbonate window or with printer flap. Fitted with partition for the tower compartment with galvanised storage shelf, pull-out shelf (load capacity 45 kg) with strain relief. Keyboard drawer with recessed and removable storage tray, palm rest made from bamboo and strain relief. Locking with a common key. Cable pass-through on the rear of the housing. Storage shelf made of bamboo.

**Colour:**

Body and keyboard drawer RAL 7035 light grey, doors, drawer front and pull-out shelf RAL 7016 anthracite **powder-coated**.

**Note:**

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

**Technical description**

Weight	97 kg
Height	1020 mm
Depth	700 mm

Depth in G	28
Width	1000 mm
Width in G	40
Support cabinet usable width right	223 mm
Support cabinet usable height	645 mm
Support cabinet usable width left	700 mm
Power supply	Mains operated
On/Off switch	yes
Plug type, input	L
Nominal voltage	250 V
Material thickness	0.9 mm
Door opening angle	250 degrees
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Computer workstation

---

## Accessories

Slide handle for GridLine Type GP11	914226 GP11
-------------------------------------	-------------