

Garant GRIDLINE

Computer workstation, Type: DK**Order data**

Order number	948201 DK
GTIN	4062406074203
Item class	9GS

Description**NOTE: Colour selection possible****Version:**

Cupboard with separately lockable double swing doors with polycarbonate window, equipped with dividing wall (can be mounted on the left or right), **pull-out shelf load capacity 45 kg**, with cable strain relief and galvanised storage shelf for the tower compartment. Locking with a common key. All the electrical items are fitted so that they do not protrude and are easily accessible. Storage shelf made of bamboo.

Colour:

Body RAL 7035 light grey, doors, drawer and pull-out shelves RAL 7016 anthracite, **powder-coated.**

Note:

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Colour selection: RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

Height: 1000 mm

Width: 1000 mm

Depth: 700 mm

Width in G: 40

Depth in G: 28

Support cabinet usable height: 645 mm

Technical description

Width in G	40
Width	1000 mm
Weight	97 kg
Depth	700 mm
Height	1020 mm
Depth in G	28
Support cabinet usable height	645 mm
Support cabinet usable width right	223 mm
Support cabinet usable width left	700 mm
Power supply	Mains operated
Nominal voltage	250 V
On/Off switch	yes
Plug type, input	K
Material thickness	0.9 mm
Door opening angle	250 °
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Computer workstation

Accessories

Slide handle for GridLine Type GP11	914226 GP11
-------------------------------------	-------------