

Garant GRIDLINE

**Computer workstation with printer flap, mobile, Type: FR****Order data**

Order number	948222 FR
GTIN	4062406074364
Item class	9GS

**Description****Version:**

Computer cabinet with separately lockable double-leaf door with polycarbonate window or with printer flap. Fitted with partition for the tower compartment with galvanised storage shelf, pull-out shelf (load capacity 45 kg) with strain relief. Keyboard drawer with recessed and removable storage tray, palm rest made from bamboo and strain relief. Locking with a common key. Cable pass-through on the rear of the housing. Storage shelf made of bamboo.

With mobile base composed of 2 fixed wheels and 2 electrically conductive castors with brakes Ø 125 mm and push handles.

**Colour:**

Body and keyboard drawer RAL 7035 light grey, doors, drawer front and pull-out shelf RAL 7016 anthracite **powder-coated**.

**Technical description**

Dimensions printer flap	346×290 mm
Depth in G	28
Height	1170 mm
Weight	97 kg

Width in G	40
Depth	700 mm
Width	1000 mm
Support cabinet usable height	645 mm
Support cabinet usable width right	223 mm
Support cabinet usable width left	700 mm
Plug type, input	E
Nominal voltage	250 V
On/Off switch	yes
Material thickness	0.9 mm
Door opening angle	250 degrees
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Computer workstation

---

## Accessories

Slide handle for GridLine Type GP11	914226 GP11
-------------------------------------	-------------