

Garant GRIDLINE

TFT monitor housing, Type: 1**Order data**

Order number	948401 1
GTIN	4062406074630
Item class	9GS

Description**Version:**

TFT monitor housing for flat screens, lockable, with fixed storage shelf. Self-supporting steplessly adjustable lift door with polycarbonate window.

Function:

IP41: Protected against water falling vertically and protected against penetration by foreign bodies with $\varnothing > 1$ mm, however tools and wires should be kept away.

Colour:

Body RAL 7035 light grey, lift doors RAL 7016 anthracite **powder-coated**.

Technical description

Monitor housing usable depth top	150 mm
Width	750 mm
Weight	21 kg
Height	600 mm
Monitor housing usable depth bottom	230 mm
Depth bottom	275 mm
Depth top	200 mm

Monitor housing usable width	690 mm
Monitor housing usable height	460 mm
IP Index of Protection	IP 41
Material thickness	0.9 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Monitor housing

Accessories

Slide handle for garment lockers without cylinder insert	914221
Slide handle for GridLine Type GP11	914226 GP11