

Garant GRIDLINE

Computer workstation with printer flap, Type: IT**Order data**

| | |
|--------------|---------------|
| Order number | 948252 IT |
| GTIN | 4062406074531 |
| Item class | 9GS |

Description**Version:**

Computer cabinet with separately lockable double-leaf door with polycarbonate window or with printer flap. Fitted with partition for the tower compartment with galvanised storage shelf, pull-out shelf (load capacity 45 kg) with strain relief. Keyboard drawer with recessed and removable storage tray, palm rest made from bamboo and strain relief. Locking with a common key. Cable pass-through on the rear of the housing. Storage shelf made of bamboo.

With space-saving TFT monitor housing for flat screens, lockable, with storage compartment for cables. Self-supporting steplessly adjustable lift door with polycarbonate window.

Colour:

Body and keyboard drawer RAL 7035 light grey, doors, drawer front and pull-out shelf RAL 7016 anthracite **powder-coated**.

Note:

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

| | |
|------------|--------|
| Weight | 120 kg |
| Depth in G | 28 |

| | |
|------------------------------------|--|
| Monitor housing usable depth | 230 mm |
| Monitor housing usable width | 690 mm |
| Height | 1620 mm |
| Depth | 700 mm |
| Width | 1000 mm |
| Monitor housing usable height | 460 mm |
| Width in G | 40 |
| Dimensions printer flap | 346x290 mm |
| Support cabinet usable width right | 223 mm |
| Support cabinet usable width left | 700 mm |
| Support cabinet usable height | 645 mm |
| Power supply | Mains operated |
| Nominal voltage | 250 V |
| Plug type, input | L |
| On/Off switch | yes |
| Material thickness | 0.9 mm |
| Door opening angle | 250 degrees |
| Cylinder lock | modular barrel |
| Colour selection | RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003 |
| Type of product | Computer workstation |

Accessories

| | |
|--|-------------|
| Slide handle for garment lockers without cylinder insert | 914221 |
| Slide handle for GridLine Type GP11 | 914226 GP11 |