

**Adjustable spanner, overall length: 300mm****Order data**

Order number	814002 300
GTIN	4062406074685
Item class	82A

**Description****Version:**

Slim design with double-T-profile shank. Jaw angle 22°. Drop-forged and hardened. With **scale** on the jaw.

Adjustable spanner, phosphated.

**Technical description**

overall length	300 mm
overall length	12 in
maximum width across flats	34 mm
Jaw position	22 degrees
Manufacturing process	drop-forged and hardened
non-sparking	no
Scaling	yes
Grips	no
Type of product	Adjustable spanners