



Adjustable spanner, overall length: 200mm



Order data

Order number	814002 200
GTIN	4062406074661
Item class	82A

Description

Version:

Slim design with double-T-profile shank. Jaw angle 22°. Drop-forged and hardened. With **scale** on the jaw.

Adjustable spanner, phosphated.

maximum width across flats: 24 mm

overall length: 8 in

Technical description

maximum width across flats	24 mm
overall length	8 in
overall length	200 mm
Jaw position	22°
Manufacturing process	drop-forged and hardened
non-sparking	no
Scaling	yes
Grips	no
Type of product	Adjustable spanners

