

Garant**Pair of gloves MASTER FIT, Glove size: 7****Order data**

Order number	094306 7
GTIN	4062406074883
Item class	01H

Description**Version:**

Anatomically shaped multi-purpose gloves with nitrile foam coating. Pleasant backing material with 15-gauge knitted technology of Spandex and nylon for very good touch sensitivity. Suitable both for dry working environments and for slightly oily or greasy areas. Free of DMF.

Standard:

EN 388, EN ISO 21420

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Technical description

Glove size	7
Protection category	Category II
Type of glove	Multi-purpose gloves
Series	MASTER FIT
Clothing standard	Oeko-Tex Standard 100

Glove characteristics	DMF-free
EN 388	4121X
Backing material	Nylon / Spandex
Coating	Nitrile foam
Coating variant	The palms of the hands
Application range	All-round
Application range	Precision
Length	250 mm
Colour	blue / orange
Knitted technology	15G
Application	reusable
Type of product	Multi-purpose gloves