

Garant GRIDLINE

Heavy-duty cabinet with Viewing window swing door, Height: 2000 mm**Order data**

Order number	942824 2000
GTIN	4062406075026
Item class	9GI

Description**Version:**

Empty cabinet in 40×28G. Suitable drawers: 36×24G (please order these separately).

Reinforced side walls to take **reinforced storage shelves for 200 kg** at 25 mm intervals.

Doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. Cabinets with reinforced cabinet base, without a levelling base.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves for GridLine heavy-duty cabinets see No. 942610.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Colour selection: RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

Height: 2000 mm

Width: 1000 mm

Depth: 700 mm

Width in G: 40

Depth in G: 28

Usable height: 1845 mm

Technical description

Weight	119 kg
Depth	700 mm
Usable height	1845 mm
Height	2000 mm
Depth in G	28
Width	1000 mm
Width in G	40
Material thickness	1 mm
Cabinet housing internal load capacity	1600
Door opening angle	250 degrees
Height adjustment interval	25
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Heavy-duty cabinet, empty

Accessories

Basic lighting set for GridLine cabinets with swing doors for cabinet height 2000 mm	940501 2000
Extended lighting set for GridLine cabinets with Swing doors, width 40G for cabinet height 2000 mm	940511 2000
Heavy load shelf for cabinet / compartment width in G 40	942610 40
Slide handle for GridLine Type GP11	914226 GP11