

**Garant**
**Arbor for screw-in milling cutters with thread, SK 40, Thread M × Length L1: M10X150**

**Order data**

|              |                |
|--------------|----------------|
| Order number | 301309 M10X150 |
| GTIN         | 4045197706751  |
| Item class   | 31A            |

**Description**
**Version:**

Plain design.

**Application:**

To take screw-in milling cutters with thread.

**Optional extras:**

Pull studs (PS) No. 308600 – 308806, PS wrenches No. 308820 – 308835.

**Technical description**

|                                      |            |
|--------------------------------------|------------|
| Bore $\varnothing D_1$ tolerance IT6 | 10.5 mm    |
| Overhang dimension A                 | 169 mm     |
| $\varnothing D_2$                    | 18 mm      |
| Reach $L_1$                          | 150 mm     |
| Thread M                             | M10×150    |
| $L_2$                                | 5 mm       |
| External $\varnothing D$             | 36.5 mm    |
| Adapter                              | SK 40      |
| Arbor standard                       | ISO 7388-1 |

|                                       |                          |
|---------------------------------------|--------------------------|
| Shape                                 | ADB                      |
| Balance quality G at rotational speed | G 2.5 at 25,000 rpm      |
| Concentricity                         | ≤ 3 μm                   |
| Machining strategy                    | HSC                      |
| Type of product                       | Threaded copy mill arbor |

## Accessories

|                                                                                         |           |
|-----------------------------------------------------------------------------------------|-----------|
| Pull stud 90°sealed suitable for steep tapers 40                                        | 308795 40 |
| Pull studMori-Seiki, sealed, form A suitable for steep tapers 40                        | 308625 40 |
| Pull stud, 18CrNiMo7sealed, form B suitable for steep tapers 40                         | 308615 40 |
| Pull stud Hurco 90° with fitsealed suitable for steep tapers 40                         | 308806 40 |
| Pull studsealed suitable for steep tapers 40                                            | 308660 40 |
| Pull stud 45°sealed suitable for steep tapers 40                                        | 308765 40 |
| Pull stud 45°sealed suitable for steep tapers 40                                        | 308760 40 |
| Special pull stud with no internal threadsealed suitable for steep tapers 40            | 308700 40 |
| Special pull stud with internal thread suitable for steep tapers 40                     | 308740 40 |
| Wrench for pull studsISO 7388 suitable for ISO taper size 40                            | 308830 40 |
| Pull studsealed, form A suitable for steep tapers 40                                    | 308610 40 |
| Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 40 | 308820 40 |
| Pull stud Hurco 45° with fitsealed suitable for steep tapers 40                         | 308802 40 |
| Pull studForm A suitable for steep tapers 40                                            | 308600 40 |
| Pull studsealed, form B suitable for steep tapers 40                                    | 308620 40 |
| Pull studForm B suitable for steep tapers 40                                            | 308640 40 |

|                                                                               |            |
|-------------------------------------------------------------------------------|------------|
| Pull stud 90°sealed suitable for steep tapers 40                              | 308790 40  |
| Pull studMazak, form A suitable for steep tapers 40M                          | 308670 40M |
| Pull studsealed suitable for steep tapers 40                                  | 308635 40  |
| Pull stud 60°sealed suitable for steep tapers 40                              | 308785 40  |
| Pull studMori-Seiki, sealed, form A suitable for steep tapers 40              | 308630 40  |
| Hurco 45° pull stud with 4-mm bore and fitsealed suitable for steep tapers 40 | 308801 40  |
| Pull stud, 18CrNiMo7Form A suitable for steep tapers 40                       | 308605 40  |
| Pull studsealed, form B suitable for steep tapers 40                          | 308650 40  |