


Garant
**Arbor for screw-in milling cutters with thread cylindrical form, HSK-A 63,
Thread M × Length L1: M12X100**

Order data

Order number	307042 M12X100
GTIN	4045197706980
Item class	31A

Description
Version:

Plain design.

With Balluff/RFID chip bore.

Application:

To take screw-in milling cutters with thread.

Optional extras:

Extensions No. 301358, reducers No. 301359, coolant pipe No. 309880, socket for coolant pipe No. 309890.

Note:

Solid carbide arbors and extensions for screw-in milling cutters No. 301374 – 301379 and No. 301361 – 301368.

Technical description

L ₂	5 mm
Thread M	M12×100
Reach L ₁	100 mm
Overhang dimension A	126 mm
Ø D ₂	21 mm
Bore Ø D ₁	12.5 mm

Adapter	HSK-A 63
Arbor standard	DIN 69893
Arbor standard	ISO 12164-1
Shape	A
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 3 \mu\text{m}$
Machining strategy	HSC
Type of product	Threaded copy mill arbor