

**Visoki cilindar, Duljina D (L): 50 mm****Podaci za narudžbu**

Broj narudžbe	370078 50
GTIN	2050001882257
Razred artikla	37K

Opis**Upotreba:**

Za produživanje steznih kuka br. 370071.
maksimalan okretni moment: 49 Nm

Tehnički opis

Duljina D (L)	50 mm
Navoj M	M12
Vanjski Ø D	40 mm
maskimalan okretni moment	49 Nm
Vrsta proizvoda	Stezni sustav naprave